

PRODUCT REQUIREMENT SHEET

See LV 75-32

| | |
|---------------------------|-----------------------------|
| MEASURING VOLTAGE | 235V (stabilisation 3 min.) |
| MEASURING POSITION | Horizontal |
| LIFE TEST POSITION | Vertical |
| BURNING POSITION | Any |
| SWITCHING CYCLE | Continuous |
| AGEING | 1h at rated voltage |

| | | VALUE UNIT | TOLERANCE |
|--------------------------|-----------------------------------|------------------|-------------------------|
| WATTAGE | | 1500W | ± 6 % |
| LIFE | | 5000 h | average |
| COLOR TEMPERATURE | Clear lamp Lamp with reflector | 2300 K NA | ± 100 K |
| FLUX (HeLeN lamp) | Clear lamp Reduction | 10000 lm 95 % | Indicative value min |
| WEIGHT | | 53 g | |

| | | | | | | | | | | | | | | | |
|---|------|-------------------------|------|---------------|------|------------|------------|--------------------|----|----|------------|----|--|----|--|
| 1 | 0833 | 2 | 0833 | 3 | 0000 | 4 | | 5 | | 6 | | 7 | | 8 | |
| SUPERSEDES : | | HALOGEN LAMP | | | | | | 9245 798 44900 | | | 12/07/2012 | | | | |
| 9245 798 44900 | | INFRARED HeLeN | | | | | | 0833/000 | | | | | | | |
| 0833/000 p. 190-2 | | 15059Z 1500W 235V | | | | | | | | | | | | | |
| Of 04/10/2010 | | REF. : PDM IRK 2011-016 | | DOCUMENTATION | | UNIT mm | PROJ EUROP | 2 | SH | SH | 190-2 | 10 | | A4 | |
| NOM : J.P. CHARLIER | | VALIDATION : A. PICHARD | | | | | | DR. FISCHER Europe | | | | | | | |
| All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner. | | | | | | | | | | | | | | | |