

PRODUCT REQUIREMENT SHEET

See LV 75-32

| | |
|--------------------|-----------------------------|
| MEASURING VOLTAGE | 400V (stabilisation 3 min.) |
| MEASURING POSITION | Horizontal |
| LIFE TEST POSITION | Horizontal |
| BURNING POSITION | P15 |
| SWITCHING CYCLE | Continuous |
| AGEING | 1h at rated voltage |

| | VALUE UNIT | TOLERANCE |
|-------------------|-----------------------------------|---|
| WATTAGE | 2500W | ± 6 % |
| LIFE | 5000 h | average |
| COLOR TEMPERATURE | Clear lamp Lamp with reflector | 2700 K 2600 K ± 100 K Indicative value |
| FLUX (HeLeN lamp) | Clear lamp Reduction | NA NA |
| WEIGHT | 45 g | |

Project

| | | | | | | | | | | | | | | | |
|---|---------------|--|------------|------------|------|--------------------|----|----------------|----|---|------------|---|--|---|--|
| 1 | 0833 | 2 | 0833 | 3 | 0000 | 4 | | 5 | | 6 | | 7 | | 8 | |
| SUPERSEDES : | | HALOGEN LAMP INFRARED INDUSTRIAL REFLECTOR 14275Z/98 2500W 400V REFL | | | | | | 9246 054 49100 | | | 28/01/2016 | | | | |
| New | | | | | | | | 0833/000 | | | | | | | |
| REF. : | CRP 1601 | DOCUMENTATION | UNIT mm | PROJ EUROP | 2 | SH | SH | 190-2 | 10 | | A4 | | | | |
| NOM : | J.P. CHARLIER | VALIDATION : A. PICHARD | | | | DR. FISCHER Europe | | | | | | | | | |
| All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner. | | | | | | | | | | | | | | | |