

# 64261 HLX

Low-voltage halogen lamps without reflector



#### Areas of application

- Lamps for special luminaires
- Medical fiber optics (HLX)

#### **Product benefits**

- Compared to standard lamps up to 10 % higher luminous efficacy (HLX)
- Instant light (HLX)

#### **Product features**

- Xenon instead of krypton as the filler gas (XENOPHOT HLX versions)
- Luminous flux up to 10 % higher with same power consumption (XENOPHOT HLX versions)
- HLX tungsten halogen low-voltage lamp with or without reflector
- Dimmable (HLX)





# Product datasheet

#### Technical data


### **Electrical data**

Nominal voltage	12.0 V
Nominal wattage	30.00 W

#### Photometrical data

Color temperature	3300 K
Nominal luminous flux	750 lm

## Dimensions & weight



Diameter	11.5 mm
Length	44.0 mm
Light center length (LCL)	30.0 mm
Filament length	2.60 mm
Illuminated field 2.6*1.3 mm <sup>2</sup>	
Filament diameter	1.3 mm

### Lifespan

Lifespan	50 h

# Additional product data

# Capabilities

Rurning position	Anv
Burning position	Ally

### Certificates & standards

EEI – Energy Label	В
--------------------	---

# Product datasheet

# **Country specific categorizations**

LIF	M/130	
Order reference	64261 30W 12V G	

### Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4050300220529	OSRH6426140	-	-	-

### Product datasheet





s180

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300220529	64261 HLX	Folding carton box 1	25 mm x 23 mm x 70 mm	0.04 dm <sup>3</sup>	5.00 g
4050300890364	64261 HLX	Shipping carton box 40	144 mm x 107 mm x 121 mm	1.86 dm <sup>3</sup>	241.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

#### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.